



At CARTONI, we are constantly innovating and looking for ways to improve our products.

Recently, we have made some improvements to the **Maxima 30** and **Master 30**. Due to market response, we have increased the maximum drag on the Master 30 and the Maxima 30, by increasing the fluid density in both modes and making modifications within the head. This will give users a wider range of drag variety: allowing the almost freewheeling effects of zero drag to the very consistent maximum drag needed when using telephoto lenses.

The new drag modifications will be standard starting from serial number: M30139. We will offer a free factory upgrade for any existing heads but will not cover costs for shipping and duties.

If you have any questions, please contact us by clicking the button below.

CONTACT US